

8960-10 Dynamometer lb in from n-m Switch

05/05/2024 08:54:23

FAQ Article Print

Category:	LabVolt Series	Votes:	0
State:	public (all)	Result:	0.00 %
Language:	en	Last update:	19:12:33 - 03/28/2023

Keywords

8960-10 Dynamometer lb in from n-m Switch

Problem (public)

User needs to switch torque unit on 8960-10

See switches' location here:

Back front panel (Need to remove metal plate):

Bottom main board:

Solution (public)

Select the desired value on the 2 switches (1 on the bottom board and 1 on the back of the front panel).

See attached pictures.